


FASTENER GROUPS LISTED BELOW ARE USED FOR ASSEMBLY AND INSTALLATION. **SOME ASSEMBLY DRILLING IS REQUIRED.** PARTITION INSTRUCTIONS & FASTENERS ARE WITH THAT UNIT. USE KD UNIT DRAWINGS TO IDENTIFY THEIR SEPARATE PARTS. CUSTOMER SPECIFIED SHELF DIMENSIONS ARE SHOWN HERE.

SYM.	FASTENERS	QTY	DRILL
●	ASSEMBLY FASTENERS { 1/4-20 x 1 1/2" THP.SCW. { 1/4-20 HX. FLANGE NUT	(32) (32)	{ 9/32
●	{ 10-24 x 1 1/2 RHP.SCW. { 10-24 HX. FLANGE NUT	(8) (8)	{ 3/16
ⓔ	{ 10-24 x 1 1/2 RHP.SCW. { 10-24 ELASTIC L'NUT	(4) (4)	{ 3/16




ADRIAN STEEL CO.
906 JAMES STREET
ADRIAN, MI 49221
517/265-6194

DOOR KIT FOR 36" KD'S

DWG BY ECN# DATE CHK BY PACKAGE# ISS:
BDS 6071 6/5/02 S/L DK536 A
PACKAGE WEIGHT- 16.78 # REF 16042
HCG= 00 VCG= 00

ITEM	PART NO.	DESCRIPTION	QTY.
1	EP1212	END PANEL 12" FOR KD'S	2
2	BP1236	BACK PANEL, 12 x 36	1
3	16044	DOOR STOP 35"	1
4	16045	DOOR ASSEMBLY 36 (33-5/8)	1
5	21000	LOCKING T HNDL W/KEY ASCO	1
BAG00035-0 FAS FOR MISC DR KITS			1
CRT00001-0 CARTON			1

PLEASE REFER TO THE INTERIOR INSTALLATION SHEET FOR CORRECT SHELF HEIGHT BEFORE ASSEMBLY.



FASTENING PROCEDURES

1. USE NUT & BOLT THRU WHEREVER POSSIBLE.
2. USE PLUSNUTS FOR BLIND FASTENING.
3. USE SHEET METAL SCREWS IN SHEAR ONLY.

CAUTION:
DRILL THRU FLOOR WITH CARE
WATCH FOR GAS TANK, CONTROL
LINES, & ELECTRICAL WIRING.